



Spec No.: DS-20-92-0164 Effective Date: 03/11/2000 Revision: -



BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C. Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660 http://www.liteon.com/opto




LITEON LITE-ON ELECTRONICS, INC.

Property of Lite-On Only

Features

- * High Intensity.
- * Popular T-1 3/4 diameter Package.
- * Selected minimum intensities.
- * Wide viewing Angle.
- * General purpose leads.
- * Reliable and rugged.

Package Dimensions



Part No.	Lens	Source Color
LTL-307GE	Green Transparent	Green

Page :

1

of

4

Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ± 0.25 mm(.010") unless otherwise noted.
- 3. Protruded resin under flange is 1.0mm(.04") max.
- 4. Lead spacing is measured where the leads emerge from the package.
- 5. Specifications are subject to change without notice.

1410 1001 212 007 02	Part	No.	:	LTL-307GE	



LITEON LITE-ON ELECTRONICS, INC.

Property of Lite-On Only

Parameter	Maximum Rating	Unit		
Power Dissipation	100 mW			
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	120	mA		
Continuous Forward Current	30 mA 0.4 mA/°C			
Derating Linear From 50°C				
Reverse Voltage	5 V			
Operating Temperature Range	-55°C to + 100°C			
Storage Temperature Range	-55°C to + 100°C			
Lead Soldering Temperature [1.6mm(.063") From Body]	260°C for 5 Seconds			

Part No.: LTL-307GE

Page: 2 of

4



LITEON LITE-ON ELECTRONICS, INC.

Property of Lite-On Only

Electrical / Optical Characteristics at TA=25°C						
Parameter	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity	Iv	19	60		mcd	I _F = 10mA Note 1,4
Viewing Angle	2 heta 1/2		40		deg	Note 2 (Fig.6)
Peak Emission Wavelength	λр		565		nm	Measurement @Peak (Fig.1)
Dominant Wavelength	λd		569		nm	Note 3
Spectral Line Half-Width	Δλ		30		nm	
Forward Voltage	VF		2.1	2.6	v	$I_F = 20 m A$
Reverse Current	IR			100	μ A	$V_R = 5V$
Capacitance	С		35		pF	$V_F = 0$, $f = 1MHz$

Note: 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission International De L'Eclairage) eye-response curve.

- 2. $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.
- 3. The dominant wavelength, λ_d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.
- 4. The Iv guarantee should be added $\pm 15\%$.

Part No.: LTL-307GE	Page :	3	of	4	
---------------------	--------	---	----	---	--



LITE-ON ELECTRONICS, INC.

Property of Lite-On Only

