

5	4	3	2 1					1	
			CIRCUIT SIZE	DIM.A	DIM.B	DIM.C	DIM.D		
			20	13.90	9.00	12.40	12.22	H	
			30	18.90	14.00	17.40	17.22		
			40	23.90	19.00	22.40	22.22	-	
			50	28.90	24.00	27.40	27.22		
			60	33.90	29.00	32.40	32.22		
			64	35.90	31.00	34.40	34.22	-	
			70	38.90	34.00	37.40	37.22	G	
			80	43.90	39.00	42.40	42.22	-	
			84	45.90	41.00	44.40	44.22	-	
			90	48.90	44.00	47.40	47.22		
			100	53.90	49.00	52.40	52.22		
HOUSING			110	58.90	54.00	57.40	57.22	F	
TING PLANE			120	63.90	59.00	62.40	62.22		
0 +0.18			LL			l			
	ERIAL: G.F. THERN NOTE: HOUSING ERIAL: PHOSPHOI	COLOR FOR	R - 1664 (O	NLY) IS	-		TE	E	
VACCUM CAP 2. PLATING ON C 0.00076 M 0.0019 MI OVER NIC *THE PRIMARY RoHS DIRECTI CARTONS WIT	MATERIAL: STAINL ONTACTS IS AS FO INIMUM GOLD PLA NIMUM TIN PLATIN KEL PLATING OVE SHIPPING CARTO VE 2002/95/EC AND HOUT THIS LABEL	LESS STEEL OLLOWS: ATING IN CO IG IN TERMI ERALL. N WILL BE L D ELV ANNE MAY CONT	.; 0.255 THI DNTACT AF INAL AREA LABLED "C EX II OF DIF AIN PROD	CK REA, , OMPLA RECTIVE UCT WI	E 2000/5 TH LEAI	D.		D	
<ol> <li>THIS PART, WHEN MATED WITH MOLEX 1.0mm PLUG CONNECTOR SERIES 71436, CONFORMS TO MOLEX PRODUCT SPECIFICATION PS-71436-9999. REFER TO CHART ON SHEET 2 FOR MATED STACK HEIGHTS FOR THIS RECEPTACLE.</li> <li>PACKAGING SPECIFICATIONS: REFER TO CHART ON SHEET 2.</li> <li>PEGS ARE OPTIONAL. REFER TO CHART ON SHEET 2.</li> <li>VACCUM PICK &amp; PLACE CAP IS OPTIONAL . REFER TO CHART ON SHEET 2.</li> <li>THIS PART CONFORMS TO EIA STANDARD 700 AAAB FOR 1.0mm TWO-PART CONNECTORS FOR USE WITH PARALLEL PRINTED BOARDS.</li> </ol>									
9. 64-CIRCUIT RE	OF SMT TAILS: 0.7 CEPTACLE ASSEN TION PURPOSES TAMP IS WEEK, YE	MBLY WITH ONLY.						В	
SYMBOLS THIS DRAWING CONTAINS INFORMATION			NOLOGIES, LLC AND	SHOULD NOT	BE USED WITH	HOUT WRITTE	N PERMISSION		
$\overrightarrow{F} = 0 \qquad \text{mm} \qquad 4:1 \qquad \text{CURRE}$	INT REV DESC: REDRAWN	N IN NX		m		X			
ANGULAR TOL ± 0.5									
	): JKACHLIC : JKACHLIC	2019/02/01			STOMED		<u></u>		
$\boxed{\bigcirc} = 0 \xrightarrow{2 \text{ PLACES}} \pm 0.13 \text{ INITIA}$	L REVISION:	DC			STOMER			A	
		1995/04/03 1995/04/03	7143	391000		PSD 0	00 A1		
DRAFT WHERE APPLICABLE THIRD AN	GLE PROJECTION DRAWING							1	

WITHIN DIMENSIONS

₢∕──= 0

4

C-SIZE 71439

SEE TABLE

GENERAL MARKET

1 OF 2

12	11	10	9	8	7	6	5	4	3	2	1
			•								

## STANDARD

Η

G

F

E

D


С

В

CIRCUIT SIZE	RECEPTACLE ASSY. MATERIAL NUMBER	PEGS	PICK & PLACE CAP	PACKAGING SPEC. NUMBER	PACKAGING TYPE
64	71439-1164	YES	NO	PK-70873-0601	TUBE
64	71439-1364	YES	YES	PK-70873-0607	TUBE
64	71439-1464	YES	YES	PK-70873-063	TAPE & REEL
64	71439-1564	NO	NO	PK-70873-0606	TUBE
64	71439-1664	NO	YES MATTE FINISH	PK-70873-063	TAPE & REEL
64	71439-1764	NO	YES	PK-70873-0606	TUBE
64	71439-1864	NO	YES	PK-70873-063	TAPE & REEL

## RECOMMENDED PLUG/RECEPTACLE COMBINATION FOR MATED STACK HEIGHT PER EIA STANDARD 700 AAAB

MATED STACK HEIGHT	RECEPTACLE HEIGHT	RECEPTACLE SERIES NO.	PLUG HEIGHT	PLUG SERIES NO.		
11.00	7.30	71439-1***	3.30	71436-1***		
12.00	7.30	71439-1***	4.30	71436-2***		



						SYM		DRAWING CONTAIN	S INFORMATION THAT IS PROPRI	ETARY TO MOLEX	ELECTRONIC TE	CHNOLOGIES, LLC AND SI	HOULD NOT BE USE	D WITHOUT WF	RITTEN PERMISSION
								MM		C: REDRAWN	IN NX	r	nol	ex	
						The second secon		NERAL TOLERAN						<u> </u>	
						F	= 0 ANGL	ULAR TOL ± 0	5° EC NO: 610884				SY, 1.0MM BO		
						S	= 0 4 PLA	ACES ±	DRWN: TTAO03 CHK'D: JKACHL		2019/01/23 2019/02/01		ACLE CONNE	CTOR 7.30	) HIGH
						W	· ·		APPR: JKACHL		2019/02/01			IER DRAW	/ING
A						$\overline{\mathbb{C}}$		ACES ± 0	13 INITIAL REVISIO	N:		DOCUMENT NUMBER			DOC PART REVISION A
						$\square$	= 0 1 PLA	ACE ± 0 ACES ±	<sup>25</sup> DRWN: REED APPR: BIXLER		1995/04/03 1995/04/03	1 / 1 / <b>X</b>	91000	PSD	000 A1
							. <u> </u>	AFT WHERE APPLICA		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		SHEET NUMBER
DOCUMENT STATUS	P1 RELEASE DATE	2019/02/01 01:16:42	2			\$	= 0	MUST REMAIN WITHIN DIMENSIONS	$\Phi =$	C-SIZE	71439	SEE TABLE	GENERAL	MARKET	2 OF 2
FORMAT: master-tb-prod-C REVISION: H DATE: 2018/01/18 12	11	10	9	8	7	6		5	4		3	2			1

PLUG STACK HEIGHT + RECEPTACLE STACK HEIGHT <u>+ 0.40 (SOLDER PASTE ALLOWANCE)</u> = MATED STACK HEIGHT

- BOTTOMING SURFACE

P = PLUG STACK HEIGHT R = RECEPTACLE STACK HEIGHT H = MATED STACK HEIGHT